

twilight

INSTRUMENTOS DE MEDICIÓN INDUSTRIAL

Medidor industrial de pH-ORP-Temperatura, pHG-1901

SB-PHG2091

www.twilight.mx

 / [twightsadecv](https://www.facebook.com/twightsadecv)

 / [twightsadecv](https://twitter.com/twightsadecv)

 / [twightsadecv](https://www.youtube.com/twightsadecv)

pHG-1901 Industrial PH Meter

pHG-1901 industrial online PH meter is precision meter for measurement of PH value of solution. With complete functions, stable performance, simple operation and other advantages, they are optimal instruments for industrial measurement and control of PH value. Various PH electrodes can be used in pHG-1901 industrial online PH meter.

Features

LCD display, high-performance CPU chip, high-precision AD conversion technology and SMT chip technology,

Multi-parameter, temperature compensation, high precision and repeatability

US TI chips; 96 x 96 world-class shell; world-famous brands for 90% parts

The current output and alarm relay adopt optoelectronic isolating technology, strong interference immunity and the capacity of long-distance transmission.

Isolated alarming signal output, discretionary setting of upper and lower thresholds for alarming, and lagged cancellation of alarming.

High-performance operational amplifier, low temperature drift; high stability and accuracy.

Technical Indexes

1. Measuring range: 0~14.00pH, Resolution:0.01pH

2. Precision:0.05pH,±0.3℃

3. Stability:≤0.05pH/24h

4. Automatic temperature compensation: 0~100℃(pH)

5. Manual temperature compensation:0~80℃(pH)

6. Output signal: 4-20mA isolated protection output, dual current output

7. Communication interface:RS485(optional)

8. Control interface: ON/OFF relay output contact

9. Relay load: Maximum 240V 5A; Maximum 115V 10A

10. Relay delay: Adjustable

11. Current output load:Max.750Ω

12. Insulation resistance:≥20M

13. Power supply: AC220V ±22V, 50Hz ±1Hz

14. Overall dimension: 96(length)x96(width)x110(depth)mm;dimension of the hole: 92x92mm

15. Weight: 0.6kg

16. Working condition: ambient temperature:0~60℃, air relative humidity:≤90%

Except for the earth magnetic field, there is no interference of other strong magnetic field around.

Standard configuration

One secondary meter, the mounting sheath of immersed (selection), one PH electrode, three packs of standard



Ordering guide:

1. To inform whether the electrode provided is a dual or ternary complex.

2. To inform the length of the electrode cable (default as 5m).

3. To inform the installation type of the electrode: flow-through, immersed, flanged or pipe-based

twilight

INSTRUMENTOS DE MEDICIÓN INDUSTRIAL



LLÁMANOS

+52(81) 8115-1400 / +52 (81) 8173-4300

LADA Sin Costo:
01 800 087 43 75

E-mail:
ventas@twilight.mx

www.twilight.mx